

A NEW AGE IN QUALITY CONTROL

**RA VISION**

***Multiple Bobbins Quality Inspection***

**THEMA SYSTEM**  
www.themasystem.com



**Ra Vision** is an automatic instrument for the first visual control of the yarn bobbins produced into the spinning process (extrusion and take-up winders) to identify possible problems and evaluate the quality of yarn bobbins. Within the same system it can find all types of visual yarn bobbins defects.

This new tool can be installed directly on the automatic sorting system and sorting lines equipped with monorail shuttle, or other solutions, which move the spinning bobbins to the packaging system and the warehouse.


The interface with the PLC for automation management can take place through the computer network or with the assistance of simple digital exchanges. The instrument carries out the whole series of checks, automatically classifying the bobbins by quality, based on the percentage and type of defects detected.

All the detected parameters, in addition of being stored on the instrument PC, can be transmitted by a computer network (wireless or Ethernet cable) to the company management system and shared on a common DB for a complete traceability of the quality control performed and a consequent correct production management.

## RA VISION 32

A Ra Vision inserted in a module and monorail shuttle sorting line, takes up to **32 seconds** to view and simultaneously analyse precisely **32 bobbins**.

**1 sec/bobbin**



**Ra Vision** was born from the technical expertise of our team combined with our 30 years experience in the textile field, with the goal of providing objective and repetitive results. Ra Vision combines optical systems, electronic boards, mechanical parts and software code to control the quality of your bobbins. All these elements are designed and managed by Thema2.

Ra Vision is an adaptive system: Thema2 has tested Ra Vision with POY, FDY, HTY, DTY (continuous filaments) with worldwide Yarn Producer. Startup a new machine means to harmonize your know-how with the Ra Vision technology.



The Ra Vision technology patented by Thema2 uses a special acquisition hardware system to:

- **Emphasize morphological defects** that physically emerge from the bobbin outer surface, such as broken filaments, dirt, profile.
- **Soften the correct morphologies** like pattern, spiral effect.
- **Optimize image acquisition and therefore analysis times**, managing to analyse very light bobbins or very dark bobbins while maintaining very fast acquisition times.

## RA VISION 24


A Ra Vision inserted in a module and monorail shuttle sorting line, takes up to **30 seconds** to view and simultaneously analyse precisely **24 bobbins**.

## 1,25 sec/bobbin




Tool	Detected defects
1. Vertical Side Defects Hunter	Bobbin with surface yarn damaged
	Waste yarn mix in the bobbin
	Yarn being pulled out by sharp objects
	Oil stained yarn
	Polymer slurry on the bobbin surface
	Fluffs at the bobbin edge
	Broken filaments and fluss > 2-4 mm
	Broken filaments and fluss > 4-6 mm
	Broken filaments and fluss > 6 mm
	Loops > 6 mm
	Defects in the last cm
Defects near the tube	
Traverses	
2. Vertical Profile Analyser	Bobbin with poor shape
	Ridges in top and bottom shoulders
	Position of the bobbin on the tube
	Steps
3. Vertical Side Analyser	Loose bobbin, winder tension < standard
	Loose circle
	Color deviation yarn in the same bobbin
4. Transfer Tail Analyser	Stiff yarn
	No tail yarn
	Crossed tail yarn
	Double tail yarn
5. Tube Analyser	Narrow tail yarn
	Damaged tube
	Batch from tube color
6. Outer Surface Analyser	Surface yarn not removed
	Crossing angle


## TRAVERSE




## DAMAGED BOBBIN




## FLUFFS MORE THAN 6mm




## LOOPS MORE THAN 6mm




## OIL STAINS



## POLYESTER STAINS



## FLUFFS 4-6mm



## AND MORE

The Ra Vision technology uses equipment designed and engineered to find various defects on yarn bobbins.

**Several software tools** have been created, each of them allows the operator to **find a specific defect**. You can also configure your instrument with only the necessary tools.

We are always designing new software tools, depending on the Client's requirements.

## Mechanical Specifications

	RA VISION 24	RA VISION 32
Weight	3000 + 3000 kg	3500 + 3500 kg
Dimensions	430 x 202 x 300 cm	430 x 232 x 300 cm

Weight and dimension values depending on number of bobbins analysable simultaneously.  
Ra Vision does not consume compressed air.

## Bobbins Specifications

Tubes lenght	150 - 200 mm
Tubes diameter	120 - 140 mm
Bobbins diameter	180 - 440 mm

Other measures available on request and based on used technologies



## Electrical Specifications


	RA VISION 24	RA VISION 32
Max. power	32 KW	35 KW
Nominal tension	380 Vac	
Connection	3Ph + PE	
Frequency	50 / 60 Hz	
IP	IP54	
Communication port	Ethernet	

Max. power value depending on number of bobbins analysable simultaneously.

## Working Conditions

Temperatures	10/40 °C
Humidity	90% (no condensation)






In the case of a multiple analysis the tool is inserted in a line with modules and monorail shuttles, the **bobbins transported by the module are analysed by groups, always simultaneously.**


This solution can be applied to a **single side of 8,12,16 bobbins** or a double module system of **8+8, 12+12 bobbins up to 16+16 bobbins.**




## 8 + 8 BOBBINS



## 12 + 12 BOBBINS



## 16 + 16 BOBBINS



**THEMA SYSTEM**  
www.themasystem.com

**THEMA 2 S.r.l. - Headquarter & workshop:**

Via G.Puccini, 2/4 - 46024 Moglia (MN) Italy - Tel. +39 0376 556400

C.F. e P.IVA (VAT): 02300850209 - SDI: 2LCMINU

thema@themasystem.com

thema2@pec.it



Made in Italy



THEMA SYSTEM

PARTNER OF

